

ZFR 75 Z22 - INDUSTRIAL THREE PHASE



CHEMICAL-PHARMACEUTICAL



ELECTRONICS



- ✓ Side channel blower motor , powerful and silent, totally maintenance free, suitable for continuous duty
- ✓ Largest surface filter in its category
- ✓ Integrated filter cleaning system
- ✓ Complete steel construction
- ✓ Vacuum gauge to detect filter clogging
- ✓ Low noise level
- ✓ Compact and mobile
- ✓ Easy filter replacement
- ✓ Reduced downtime of machine tools
- ✓ ATEX-certified Z22



SUCTION UNIT

Atex zones	ATEX Z22	
Marking	II 3D Ex h tc IIIC T80°C (Int)/ T165°C (Ext) Dc	
Voltage	V - Hz	400 - 50 3~
Power	kW	4
Electrical protection	IP	65
Max water lift	mmH ₂ O	3.600 - 2.900
Max air flow	m ³ /h	318
Suction inlet	mm	80
Noise level (EN ISO 3744)	dB(A)	76



FILTER UNIT

Filter Type	Star	
Surface - Diameter	cm ² -mm	30.000 - 500
Material - Efficiency	IEC 60335-2-69	Polyester - ANT M
Air load on filter	m ³ /m ² /h	106
Cleaning system	Manual	



COLLECTION UNIT

Capacity	l	100
----------	---	-----



VOLUME

Dimensions	cm	79x66x190h
Weight	kg	110



SUCTION UNIT

The suction unit is a side channel blower, with direct coupling between the motor and the impeller fan. It is designed without any transmission system, and is therefore silent, totally maintenance free and suitable for continuous duty operations.

A pressure relief valve protects the motor, providing additional air for cooling.



FILTER UNIT

The large surface star filter, located inside the filter stainless steel chamber, is made of polyester and provides high resistance against clogging and passage of fine dust.

A vacuum gauge enables to check constantly the state of the filter and detect possible clogging, warning the operator that the filter must be cleaned.

It is possible to clean the filter using an integrated mechanical system: an external lever shakes the filter vertically and enables to clean the filter thoroughly and safely, maintaining constant suction performance and preventing any dispersion of dust in the environment.



COLLECTION UNIT

The vacuumed material is collected into a wheeled steel container, which can be extracted for easy disposal and can be used with optional disposable bags, for safer and handier disposal.



OPTIONALS

✓ OTHER VOLTAGES AND FREQUENCIES AVAILABLE UPON REQUEST